



IN-LINE 6T, Crimper Jaw Permanent O & D3 Grooves (Jaw Only)

By Burndy
Catalog # [PATMD68LWJAW](#)

PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, O/D3 Crimp Jaw with Permanent Grooves (Jaw Only)

Features

- Crimp jaw with permanent O/D3 grooves
- Interchangeable scissor action jaw
- Locking jaw tabs
- Uses W and X dies
- for PATMD-LW series batteries

Application

Crimping and Cutting

Specifications

Buy America(n) Qualified	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Conductor	
Crimping Ranges	Copper: #10 sol. - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil, Aluminum: #14 sol. - 350 kcmil, ACSR: #14 sol. - 4/0 AWG

Dimensions

Weight	2 lb.
Height	1.0625 in
Width	4.27 in



Length	5.06 in
Dimensions	5.06 in x 4.27 in x 1.0625 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Tool Type	Crimper Jaw
Application - For Use On	Crimping with Permanent O/D3 Die Grooves, W & X Dies
Die Type	W Die and X Die
UPC	621945483484
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC 12 Digit	621945483484
Series	PATRIOT® IN-LINE® Series

Logistics

Minimum Pack Quantity	1
Package Contents	O/D3 Crimper Jaw for PATMD-LW Tool

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)