



IN-LINE 6T, O/D3 Crimp, ACSR Cut Jaws, Util Bag, 3Ah Makita Batteries

By Burndy
Catalog # [PATMD68LWWCJ](#)

6T IN-LINE® O/D3 ACSR 3Ah AC UB



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Specifications

Buy American Compliant	No
EU RoHS Indicator	Contact Manufacturer

Conductor

Crimping Ranges	• With Appropriate Jaw: Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG • Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	18.73 in
Weight	5.55 lb.
Height	4.38 in
Width	2.75 in
Dimensions	18.73 in x 2.75 in x 4.38 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	• Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex • Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)
Trade Name	PATRIOT® IN-LINE®
Series	PATRIOT® IN-LINE® Series
Tool Type	Battery Actuated Scissor Action
Container Type	Vinyl Utility Bag
Die Type	W Die and X Die
UPC	621945480995
Type	Crimper and Cutter
UPC 12 Digit	621945480995

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, O/D3 Crimp Jaw, ACSR Cut Jaw, (2) Batteries, Charger, Utility Bag
Pallet Quantity	30
Carton Quantity	1

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)