



PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, BG/D3 Crimp Jaw, (2) 5.0Ah 18V Li-ion Batteries, 12V-DC Charger, Utility Bag

By Burndy
Catalog # PATMD6LW5DC

6T IN-LINE® BG/D3 5Ah DC UB

Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Conductor

- Crimping Ranges
- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
 - Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Current

Operating Voltage18 VDC

Dimensions

Length18.73 in
Weight5.55 lb.
Height2.75 in
Width4.375 in
Dimensions18.73 in x 4.375 in x 2.75 in



Force Related

Crimp Force Capacity6 ton

General

Application - For Use On

- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
- Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)

Trade NamePATRIOT® IN-LINE®
SeriesPATRIOT® IN-LINE® Series
Tool TypeBattery Actuated Scissor Action
Container TypeVinyl Utility Bag
Die TypeW Die and X Die
UPC621945476899
TypeCrimper and Cutter
UPC 12 Digit621945476899

Logistics

Package ContentsTool, BG/D3 Crimp Jaw, (2) Batteries, Charger, Utility Bag
Pallet Quantity30
Carton Quantity1

Operational

Recharge Time0.75 hr
Battery Type5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source12V-DC Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)