



PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, CU/AL Cut Jaw, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger

By Burndy
Catalog # [PATMDCUTCLW](#)

6T IN-LINE® CU/AL 3Ah AC UB

Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Conductor

Crimping Ranges

- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
- Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Dimensions

Length	19.42 in
Weight	5.55 lb.
Height	2.75 in
Width	4.375 in
Dimensions	19.42 in x 4.375 in x 2.75 in

Force Related



Crimp Force Capacity6 ton

General

Application - For Use On

- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
- Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)

Trade Name
Series
Tool Type

PATRIOT® IN-LINE®
PATRIOT® IN-LINE® Series
Battery Actuated Scissor Action

Container Type
Die Type
UPC
Type
UPC 12 Digit

Vinyl Utility Bag
W Die and X Die
621945528468
Crimper and Cutter
621945528468

Logistics

Minimum Pack Quantity
Package Contents

Pallet Quantity
Carton Quantity

1
Tool, CU/AL Cut Jaw, (2) Batteries, Charger, Utility Bag
30
1

Operational

Recharge Time
Battery Type

0.5 hr
3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source

120V-AC Charger

Product Assets

[Catalog \[English\]](#)