



# PATRIOT® IN-LINE® 6-Ton Scissor Action Cutter Jaw for ACSR (Jaw Only)

By Burndy  
Catalog # [PATMDCUTLWJAW](#)



PATMD-LW IN-LINE® 6T Scissor Action Cutter Jaw for ACSR (Jaw Only).

### Features

- Use with ACSR cable
- Interchangeable scissor action jaw
- Locking jaw tabs
- for PATMD-LW series

### Application

Crimping and Cutting

### General

|                          |                                             |
|--------------------------|---------------------------------------------|
| Application - For Use On | Cutting ACSR (26/7) Cable up to 556.5 kcmil |
| Catalog Number           | PATMDCUTLWJAW                               |
| Crimp Force Capacity     | 6 ton                                       |
| Die Type                 | W Die and X Die                             |
| EU RoHS Indicator        | Contact Manufacturer                        |
| Power Source             | 120V-AC Charger                             |
| Recharge Time            | 0.5 h                                       |
| Sub Brand                | PATRIOT® IN-LINE® CUTTER JAW                |
| Tool Type                | Cutter Jaw                                  |
| Trade Name               | PATRIOT® IN-LINE®                           |
| Type                     | Crimper and Cutter                          |
| UPC                      | 621945483460                                |

### Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 5.82 in x 4.58 in x 1.375 in |
| Height     | 1.375 in                     |
| Length     | 5.82 in                      |

|        |         |
|--------|---------|
| Weight | 2.5 lb  |
| Width  | 4.58 in |

### Conductor Related

|                 |                                                                                                                      |
|-----------------|----------------------------------------------------------------------------------------------------------------------|
| Crimping Ranges | Cutting Capacity: ACSR (26/7) up to 556.5 kcmil; Aluminum (AAC) up to 636 kcmil; Copper (soft drawn) up to 350 kcmil |
|-----------------|----------------------------------------------------------------------------------------------------------------------|

### Certifications And Compliance

|                          |                      |
|--------------------------|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
|--------------------------|----------------------|

### Logistics

|                       |                                   |
|-----------------------|-----------------------------------|
| Carton Quantity       | 1                                 |
| Minimum Pack Quantity | 1                                 |
| Package Contents      | ACSR Cutter Jaw for PATMD-LW Tool |
| Pallet Quantity       | 464                               |

### Product Assets

- [Brochures - PATMD-LW Trifold Brochure](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - BUR\\_PATMD-LW](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50054529](#)  
[Specifications - PATMDCUTLWJAW](#)  
[Video - BURNDY PATMD-LW](#)



A Hubbell brand