



# PENA1355GAL, Oxide Inhibitor, 55 Gallon

By Burndy  
Catalog # [PENA1355GAL](#)



Oxide Inhibiting Compound, 55 Gallon, Stored in Drum,  
Recommended for Al/Al, Al/Cu , Al/Conduit Threads ,  
Compatible W/ Rubber or Polyethylene Insulation.

### Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

### General

|                                         |                                                             |
|-----------------------------------------|-------------------------------------------------------------|
| Application - For Use On                | Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper |
| Catalog Number                          | PENA1355GAL                                                 |
| Container Type                          | Drum                                                        |
| Pour Point                              | -40 °F                                                      |
| Temperature - Dropping Point Fahrenheit | 350 °F                                                      |
| Trade Name                              | PENETROX™                                                   |
| UPC                                     | 781810023624                                                |
| UPC 14 Digit GTIN                       | 00781810023624                                              |

Viscosity at 100 Fahrenheit 250 °F

### Certifications And Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

### Logistics

|                       |           |
|-----------------------|-----------|
| Container Size        | 55 Gallon |
| Minimum Pack Quantity | 1         |

### Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[SDS - PENETROX A-13 SDS](#)  
[SDS - PENETROX A-13 ESPANOL SDS](#)  
[SDS - SDS - Dutch - Penetrox A-13](#)  
[SDS - PENETROX A-13 FRENCH SDS](#)  
[SDS - PENETROX A-13 GERMAN SDS](#)  
[SDS - PENETROX A-13 ITALIAN SDS](#)  
[SDS - PENETROX A-13 PORTUGUESE SDS](#)  
[Specifications - PENA1355GAL](#)



A Hubbell brand