



PENA255GAL, Oxide Inhibitor, 55 Gallon Container

By Burndy
Catalog # [PENA255GAL](#)

Penetrox Oxide Inhibitor Reformulations



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

General

Trade Name	PENETROX™
UPC 12 Digit	781810105887
UPC 14 Digit GTIN	00781810105887
Container Type	Drum
UPC	781810105887

Logistics

Minimum Pack Quantity	1
Container Size	55 Gallon

Product Assets

[Catalog \[English\]](#)