



PENA2BBLLB, Oxide Inhibitor

By Burndy
Catalog # [PENA2BBLLB](#)

PENETROX Oxide Inhibitor



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

General

Container Type	Drum
UPC	781810444689
Trade Name	PENETROX™

Logistics

Container Size	55 Gallon
----------------	-----------

Product Assets

[Catalog \[English\]](#)