



# PENA4, Oxide Inhibitor, 4 ounce

By Burndy  
Catalog # [PENA4](#)

Oxide Inhibiting Electrical Joint Compound, 4 OZ, For Al-Al, Al-Cu & Al Conduit Threads



## Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

## Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

## Specifications

|                                    |     |
|------------------------------------|-----|
| Buy American Compliant             | No  |
| Certification - cULus              | No  |
| EU RoHS Indicator                  | Yes |
| Certification - UL Recognized      | No  |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |
| Certification - CSA Approved       | No  |
| UL Listed                          | Yes |

## Dimensions

|                |           |
|----------------|-----------|
| Package Length | 0.000 in  |
| Package Width  | 0.000 in  |
| Package Weight | 0.000 lb. |
| Package Height | 0.000 in  |

## General

|                          |                                                                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Sub Brand                | PENETROX                                                                                                                          |
| Trade Name               | PENETROX™                                                                                                                         |
| Application - For Use On | <ul style="list-style-type: none"><li>• Aluminum to Aluminum</li><li>• Aluminum to Conduit</li><li>• Aluminum to Copper</li></ul> |
| Pour Point               | -15 °F                                                                                                                            |
| Type                     | Sealing compound                                                                                                                  |
| UPC 12 Digit             | 781810593103                                                                                                                      |
| UPC 14 Digit GTIN        | 00781810593103                                                                                                                    |
| Container Type           | Squeeze Bottle                                                                                                                    |
| UPC                      | 781810593103                                                                                                                      |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Container Size        | 4 oz |
| Carton Quantity       | 12   |
| Pallet Quantity       | 3360 |

## Operational

|                                         |        |
|-----------------------------------------|--------|
| Temperature - Dropping Point Fahrenheit | 230 °F |
| Viscosity at 100 Fahrenheit             | 305 °F |

## Product Assets

[Catalog \[English\]](#)