



PENA5GAL, Oxide Inhibitor, 5 Galloon Container

By Burndy
Catalog # [PENA5GAL](#)



Electrical Joint Compound, 5 Gallon Steel Pail, 28/26 Gauge-Black, For Al-Al and Al-Cu Connectors ,Grounding, Cu Conduit Threads.

Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA5GAL
Container Type	Pail
Pour Point	-15 °F
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
UPC	781810592830

UPC 14 Digit GTIN	00781810592830
Viscosity at 100 Fahrenheit	305 °F

Certifications And Compliance

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1
Container Size	5 Gallon
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PENAGAL_LineArt](#)
- [Sales Drawings - 50016091](#)
- [SDS - PENETROX A PORTUGUESE SDS](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A ESTONIAN SDS](#)
- [SDS - PENETROX A FRENCH SDS](#)
- [SDS - PENETROX A ESPANOL SDS](#)
- [SDS - PENETROX A SDS](#)
- [Specifications - PENA5GAL](#)



A Hubbell brand