



PENE5GAL, Oxide Inhibitor, 5 Gallon Container

By Burndy
Catalog # [PENE5GAL](#)



Electrical Joint Compound, 5 Gallon Steel Pail, 28/26 Gauge-Black, For Cu/Cu Applications ,Grounding, Cu Conduit Threads.

Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

General

Application - For Use On	Copper to Copper
Catalog Number	PENE5GAL
Container Type	Pail
Pour Point	-40 °F
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
UPC	781810023617
UPC 14 Digit GTIN	00781810023617
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1
Container Size	5 Gallon
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_PENEQT_LineArt](#)
[Sales Drawings - 50016181](#)
[SDS - PENETROX E PORTUGUESE SDS](#)
[SDS - PENETROX E GERMAN SDS](#)
[SDS - PENETROX E Polish SDS](#)
[SDS - PENETROX E FRENCH SDS](#)
[SDS - PENETROX E RUSSIAN SDS](#)
[SDS - PENETROX E ESPANOL SDS](#)
[SDS - PENETROX E SDS](#)
[Specifications - PENE5GAL](#)



A Hubbell brand