



PENEGAL, Oxide Inhibitor, Gallon Container

By Burndy
Catalog # [PENEGAL](#)



Electrical sealing compound, For Use On-Application: Copper to Copper.

Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

General

Application - For Use On	Copper to Copper
Catalog Number	PENEGAL
Container Type	Can
Pour Point	-40 °F
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
UPC	781810593509
UPC 14 Digit GTIN	00781810593509
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	2
Container Size	1 Gallon
Minimum Pack Quantity	1

Product Assets

- [3D Models - PENEGAL_MODEL-IGES](#)
- [3D Models - PENEGAL_MODEL-STEP](#)
- [3D Models - PENEGAL_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PENEQT_LineArt](#)
- [SDS - PENETROX E PORTUGUESE SDS](#)
- [SDS - PENETROX E GERMAN SDS](#)
- [SDS - PENETROX E Polish SDS](#)
- [SDS - PENETROX E FRENCH SDS](#)
- [SDS - PENETROX E RUSSIAN SDS](#)
- [SDS - PENETROX E ESPANOL SDS](#)
- [SDS - PENETROX E SDS](#)
- [Specifications - PENEGAL](#)