



PENHT8, Oxide Inhibitor, 8 Ounce Container

By Burndy
Catalog # [PENHT8](#)

HiTemp Pen 8oz



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

UL Listed

No

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in

General

Trade Name	PENETROX™
Pour Point	-58 °F
UPC 12 Digit	781810476567
UPC 14 Digit GTIN	00781810476567
Container Type	Squeeze Bottle
UPC	781810476567

Logistics

Minimum Pack Quantity	1
Container Size	8 oz

Product Assets

[Catalog \[English\]](#)