



PGN1025X03B, Nylon Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [PGN1025X03B](#)

Nylon Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03)

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	Male/Female Quick Disconnect
----------------	------------------------------

Dimensions



Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm
Dimension - B Length fraction	0.27
Dimension - B Length inch	0.27 in
Dimension - L Length Overall mm	24 mm
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.95 in

General

Insulation Type	Nylon
Trade Name	FINGRIP™
Plated	Y
Insulation Type	Y
Type	Disconnect Connectors
UPC 12 Digit	781810327265
UPC 14 Digit GTIN	00781810327265
Material	Brass
Plating Type	Tin
UPC	781810327265

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)