



PGN1425X03D, Nylon Male/Female  
Combination Quick Disconnect For 16 - 14  
AWG (.25 x .03)

By Burndy  
Catalog # [PGN1425X03D](#)

Nylon Male/Female Combination Quick Disconnect For 16 - 14  
AWG (.25 x .03)

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

Specifications

|                               |    |
|-------------------------------|----|
| Certification - cULus         | No |
| Certification - UL Recognized | No |
| Certification - ETL           | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - CSA Approved  | No |
| UL Listed                     | No |

Conductor

|                 |                                                                                           |
|-----------------|-------------------------------------------------------------------------------------------|
| Conductor Size  | 16 - 14 AWG                                                                               |
| Conductor Type  | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |
| Conductor Range | #14 AWG to #16 AWG                                                                        |

Configuration

|                |                              |
|----------------|------------------------------|
| Connector Type | Male/Female Quick Disconnect |
|----------------|------------------------------|

Dimensions

|                        |          |
|------------------------|----------|
| Dimension - Width inch | 0.28 in  |
| Package Length         | 0.000 in |
| Dimension - Width mm   | 7 mm     |



|                                           |           |
|-------------------------------------------|-----------|
| Package Width                             | 0.000 in  |
| Dimension - F Width Center to Center inch | 0.09 in   |
| Dimension - B Length fraction             | 0.17      |
| Package Weight                            | 0.000 lb. |
| Dimension - B Length inch                 | 0.17 in   |
| Dimension - L Length Overall mm           | 23 mm     |
| Package Height                            | 0.000 in  |
| Dimension - Strip Length inch             | 3/8 in    |
| Dimension - Length Overall inch           | 0.87 in   |

General

|                   |                       |
|-------------------|-----------------------|
| Insulation Type   | Nylon                 |
| Trade Name        | FINGRIP™              |
| Plated            | Y                     |
| Insulation Type   | Y                     |
| Type              | Disconnect Connectors |
| UPC 12 Digit      | 781810293102          |
| UPC 14 Digit GTIN | 00781810293102        |
| Material          | Brass                 |
| Plating Type      | Tin                   |
| UPC               | 781810293102          |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 50  |
| Carton Quantity       | 600 |

Product Assets

[Catalog \[English\]](#)