



PGP1025X03D, Vinyl Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy

Catalog # [PGP1025X03D](#)

Vinyl Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03)

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	Male/Female Quick Disconnect
----------------	------------------------------

Dimensions

Package Height	0.000 in
----------------	----------



Dimension - B Length fraction	0.27
Package Weight	0.000 lb.
Dimension - Width mm	7 mm
Dimension - Width inch	0.28 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	24 mm
Dimension - B Length inch	0.27 in
Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	3/8 in

General

Plated	Y
Insulation Type	Vinyl
Trade Name	FINGRIP™
UPC	781810293089
Type	Disconnect Connectors
Insulation	Y
Material	Brass
Plating Type	Tin
UPC 12 Digit	781810293089
UPC 14 Digit GTIN	00781810293089

Logistics

Pallet Quantity	17970
Carton Quantity	600

Product Assets

[Catalog \[English\]](#)



A Hubbell brand