



PGP1425X03B, Vinyl Male/Female
Combination Quick Disconnect For 16 - 14
AWG (.25 x .03)

By Burndy
Catalog # [PGP1425X03B](#)

Vinyl Male/Female Combination Quick Disconnect For 16 - 14
AWG (.25 x .03)

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Male/Female Quick Disconnect
----------------	------------------------------

Dimensions

Dimension - Width inch	0.28 in
Package Length	0.000 in
Dimension - Width mm	7 mm
Package Width	0.000 in



Dimension - B Length fraction	0.17
Package Weight	0.000 lb.
Dimension - B Length inch	0.17 in
Dimension - L Length Overall mm	23 mm
Package Height	0.000 in
Dimension - Inside Diameter inch	0.091 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.91 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Disconnect
Trade Name	FINGRIP™
Color	Blue
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810327203
UPC 14 Digit GTIN	00781810327203
Material	Brass
Plating Type	Tin
UPC	781810327203

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)