



PGP1425X03D, Vinyl Male/Female
Combination Quick Disconnect For 16 - 14
AWG (.25 x .03)

By Burndy
Catalog # [PGP1425X03D](#)

Vinyl Male/Female Combination Quick Disconnect For 16 - 14
AWG (.25 x .03)

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Male/Female Quick Disconnect
----------------	------------------------------

Dimensions

Dimension - Width inch	0.28 in
Package Length	0.000 in
Dimension - Width mm	7 mm



Package Width	0.000 in
Dimension - F Width Center to Center inch	0.09 in
Dimension - B Length fraction	0.17
Package Weight	0.000 lb.
Dimension - B Length inch	0.17 in
Dimension - L Length Overall mm	23 mm
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.91 in

General

Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810293072
UPC 14 Digit GTIN	00781810293072
Material	Brass
Plating Type	Tin
UPC	781810293072

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)