



PGP1825X03B, Vinyl Male/Female
Combination Quick Disconnect For 22 - 18
AWG (.25 x .03)

By Burndy
Catalog # [PGP1825X03B](#)

Vinyl Male/Female Combination Quick Disconnect For 22 - 18
AWG (.25 x .03)

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#18 AWG to #22 AWG

Configuration

Connector Type	Male/Female Quick Disconnect
----------------	------------------------------

Dimensions

Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm
Dimension - B Length fraction	0.17



Dimension - B Length inch	0.17 in
Dimension - L Length Overall mm	23 mm
Dimension - Inside Diameter inch	0.067 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.91 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Disconnect
Trade Name	FINGRIP™
Color	Red
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810327197
UPC 14 Digit GTIN	00781810327197
Material	Brass
Plating Type	Tin
UPC	781810327197

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)