



Hydraulic Hose, 10', 3/16" dia non-cond,
Stackable couplers (male/female), Orange,
Min burst pressure 40,000 psi, Nom
working pressure 10,000 psi

By Burndy
Catalog # [PT2990010](#)

Hydraulic Hose N/C, 3/16", 10', 10K psi

Features

- Non Conductive
- 10' x 3/16" diameter
- Stackable male/female couplers
- Safety Orange
- For use with 10,000 psi pumps

Application

Accessory, Hose

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Standards - RoHS Compliance	EX
Status	
Buy America(n) Qualified	Contact Manufacturer

Dimensions



Width	0.187 in
Weight	4.25 lb.
Height	0.187 in
Length	15.25 in
Dimensions	15.25 in x 0.187 in x 0.187 in

General

Sub Brand	TOOLING ACCESSORY
Type	Hydraulic Accessories
UPC	781810625668

Logistics

Package Contents	Hose, Couplers
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)