



Hydraulic Hose, 25', 3/16" dia non-cond,
Stackable couplers (male/female), Orange,
Min burst pressure 40,000 psi, Nom
working pressure 10,000 psi

By Burndy
Catalog # [PT2990025](#)

Hydraulic Hose N/C, 3/16", 25', 10K psi

Features

- 10,000 PSI
- Orange
- Non-Conductive
- Stackable couplers (male/female)

Application

Accessory

Specifications

EU RoHS Indicator	Yes
Standards - RoHS Compliance	EX
Status	
Buy America(n) Qualified	Contact Manufacturer

Dimensions



Width	0.187 in
Weight	5.64 lb.
Height	0.187 in
Length	30.25 in
Dimensions	30.25 in x 0.187 in x 0.187 in

General

Type	Hydraulic Hose
UPC	781810008478

Logistics

Package Contents	Hose, Couplers
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)