



Hydraulic Hose, 10', 1/4" dia non-cond,  
Stackable couplers (male/female), Orange,  
Min burst pressure 40,000 psi, Nom  
working pressure 10,000 psi

By Burndy  
Catalog # [PT2990110](#)

Hydraulic Hose N/C, 1/4", 10', 10K psi

Features

- Non Conductive
- 10' x 1/4" diameter
- Stackable male/female couplers
- Safety Orange
- For use with 10,000 psi pumps

Application

Accessory, Hose

Specifications

|                                    |     |
|------------------------------------|-----|
| Buy American Compliant             | No  |
| EU RoHS Indicator                  | Yes |
| Standards - RoHS Compliance Status | EX  |

Dimensions



|            |                              |
|------------|------------------------------|
| Width      | 0.25 in                      |
| Weight     | 4.50 lb.                     |
| Height     | 0.25 in                      |
| Length     | 15.25 in                     |
| Dimensions | 15.25 in x 0.25 in x 0.25 in |

General

|           |                       |
|-----------|-----------------------|
| Sub Brand | TOOLING ACCESSORY     |
| Type      | Hydraulic Accessories |
| UPC       | 781810008485          |

Logistics

|                       |                |
|-----------------------|----------------|
| Package Contents      | Hose, Couplers |
| Minimum Pack Quantity | 1              |

Product Assets

[Catalog \[English\]](#)