



PTV10, Vinyl Pin Terminal For 12 - 10 AWG

By Burndy
Catalog # [PTV10](#)

Vinyl Pin Terminal For 12 - 10 AWG



Features

- Vinyl Insulation
- Color-coded barrels
- Provides an easy and effective way to terminate stranded wire into European/Metric-style terminal blocks

Specifications

Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)

Conductor

Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Pin Terminal
----------------	--------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.27 in
Dimension - Pad Size inch	0.50 in
Dimension - Pad Width inch	0.11 in
Package Height	0.000 in
Dimension - Strip Length inch	5/16 in
Dimension - Length Overall inch	0.97 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
UPC 12 Digit	781810530627
UPC 14 Digit GTIN	00781810530627
UPC	781810530627

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)