



PTV14, Vinyl Pin Terminal For 16 - 14 AWG

By Burndy
Catalog # [PTV14](#)

Vinyl Pin Terminal For 16 - 14 AWG



Features

- Vinyl Insulation
- Color-coded barrels
- Provides an easy and effective way to terminate stranded wire into European/Metric-style terminal blocks

Application

Used to terminate standard wires,creating a quality ,reliable connection by ensuring each wire strand conducts current when properly crimped

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)

Conductor

Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Pin Terminal
----------------	--------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.19 in
Dimension - Pad Size inch	0.41 in
Dimension - Pad Width inch	0.07 in
Package Height	0.000 in
Size	16-14 AWG
Dimension - Strip Length inch	5/16 in
Dimension - Length Overall inch	0.8 in

General

Sub Brand	VINYLUG
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Type	PTV
UPC 12 Digit	781810530610
UPC 14 Digit GTIN	00781810530610
UPC	781810530610

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)