



Q10F25X03B, Uninsulated Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [Q10F25X03B](#)



Uninsulated Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Specifications

Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	UI
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Dimensions

Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.66 in

General

Trade Name	FINGRIP™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Disconnect Connectors
Material	Brass
Plating Type	Tin
UPC	781810292860

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	49500

Product Assets

[Catalog \[English\]](#)