



Q10M25X03D, Uninsulated Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [Q10M25X03D](#)

Uninsulated Male Quick Disconnect For 12 - 10 AWG (.25 x .03)



Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Application

Male Disconnect

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Dimensions

Dimension - Width inch	0.250 in
Dimension - Width mm	6 mm
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.66 in

General

Sub Brand	HYDENT
Trade Name	FINGRIP™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Disconnect Connectors
UPC 12 Digit	781810525036
UPC 14 Digit GTIN	00781810525036
Material	Brass
Plating Type	Tin
UPC	781810525036

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand