



Q14F11X02B, Uninsulated Female Quick Disconnect For 16 - 14 AWG (.11 x .02)

By Burndy
Catalog # [Q14F11X02B](#)



Uninsulated Female Quick Disconnect For 16 - 14 AWG (.11 x .02)

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Specifications

Standards - RoHS Compliance UI
Status

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type Female Quick Disconnect

Dimensions

Dimension - Width inch	0.110 in
Dimension - Width mm	3 mm
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.66 in

General

Trade Name	FINGRIP™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Disconnect Connectors
UPC 12 Digit	781810355626
UPC 14 Digit GTIN	00781810355626
Material	Brass
Plating Type	Tin
UPC	781810355626

Logistics

Minimum Pack Quantity 1000

Product Assets

[Catalog \[English\]](#)