



Q14F25X03D, Female Quick Disc, 16-14 AWG (.25 x .03)

By Burndy
Catalog # [Q14F25X03D](#)

Uninsulated Female Quick Disconnect For 16 - 14 AWG (.25 x .03),
Butted Seam

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

For quickly connecting or disconnecting a terminal

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------



Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Width mm	6 mm
Dimension - Width inch	0.250 in
Dimension - Length Overall inch	0.66 in

General

Product Family	COMPRESSION
Trade Name	FINGRIP™
Feature - Barrel Style	Chamfered
Plated	Yes
Sub Brand	FINGRIP
Product Type	Terminal
UPC	781810293362
Type	Disconnect Connectors
Material	Brass
Plating Type	Tin
UPC 12 Digit	781810293362
UPC 14 Digit GTIN	00781810293362

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)