



Q14M25X03B, Uninsulated Male Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy
Catalog # [Q14M25X03B](#)



Uninsulated Male Quick Disconnect For 16 - 14 AWG (.25 x .03)

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Dimensions

Dimension - Width inch	0.25 in
Package Length	0.000 in
Dimension - Width mm	6 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.66 in

General

Trade Name	FINGRIP™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Disconnect Connectors
UPC 12 Digit	781810292792
UPC 14 Digit GTIN	00781810292792
Material	Brass
Plating Type	Tin
UPC	781810292792

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)