

Q18F18X02B, Uninsulated Female Quick Disconnect For 22 - 18 AWG (.19 x .02)



By Burndy
Catalog # [Q18F18X02B](#)

Uninsulated Female Quick Disconnect For 22 - 18 AWG (.19 x .02).

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

General

Catalog Number	Q18F18X02B
Connector Type	Female Quick Disconnect
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327272
UPC 14 Digit GTIN	00781810327272

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - F Width Center to Center inch	0.10 in
Dimension - Length Overall inch	0.58 in
Dimension - Width inch	0.20 in
Dimension - Width mm	5 mm

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094205](#)
[Specifications - Q18F18X02B](#)