



Q18F25X03D, Uninsulated Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [Q18F25X03D](#)

Uninsulated Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

For quickly connecting or disconnecting a terminal

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	• 20 AWG • 18 AWG
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size



Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Dimensions

Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.250 in
Dimension - Width mm	6 mm
Dimension - Length Overall inch	0.66 in

General

Trade Name	FINGRIP™
Sub Brand	FINGRIP
Plated	Y
Feature - Barrel Style	Chamfered
Type	Disconnect Connectors
UPC 12 Digit	781810293164
UPC 14 Digit GTIN	00781810293164
Material	Brass
Plating Type	Tin
UPC	781810293164

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)