



Q18M25X03B, Uninsulated Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [Q18M25X03B](#)

Uninsulated Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	• 20 AWG • 18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Dimensions

Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall	0.66 in

General

Trade Name	FINGRIP™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Disconnect Connectors
UPC 12 Digit	781810327562
UPC 14 Digit GTIN	00781810327562
Material	Brass
Plating Type	Tin
UPC	781810327562

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)