



## Q18M25X03D, Uninsulated Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy

Catalog # [Q18M25X03D](#)

Uninsulated Male Quick Disconnect For 22 - 18 AWG (.25 x .03)



### Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

### Application

For quickly connecting or disconnecting a terminal

### Specifications

|                               |                      |
|-------------------------------|----------------------|
| Buy American Compliant        | Contact Manufacturer |
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Yes                  |
| Certification - UL Recognized | No                   |
| Buy America(n) Qualified      | Contact Manufacturer |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| Certification - CSA Approved  | No                   |
| UL Listed                     | No                   |

### Conductor

|                                   |                                                                                           |
|-----------------------------------|-------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 20 AWG</li><li>• 18 AWG</li></ul>                 |
| Conductor Size                    | 22 - 18 AWG                                                                               |
| Conductor - Copper Str Size Range | 20 AWG - 18 AWG                                                                           |
| Conductor Type                    | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |

### Configuration

|                |                       |
|----------------|-----------------------|
| Connector Type | Male Quick Disconnect |
|----------------|-----------------------|

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Strip Length inch   | 3/8 in   |
| Dimension - Width inch          | 0.250 in |
| Dimension - Width mm            | 6 mm     |
| Dimension - Length Overall inch | 0.66 in  |

### General

|                        |                       |
|------------------------|-----------------------|
| Trade Name             | FINGRIP™              |
| Sub Brand              | FINGRIP               |
| Plated                 | Y                     |
| Feature - Barrel Style | Chamfered             |
| Type                   | Disconnect Connectors |
| UPC 12 Digit           | 781810293263          |
| UPC 14 Digit GTIN      | 00781810293263        |
| Material               | Brass                 |
| Plating Type           | Tin                   |
| UPC                    | 781810293263          |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Carton Quantity       | 1200  |
| Pallet Quantity       | 99999 |

### Product Assets

[Catalog \[English\]](#)



A Hubbell brand