



Q2B312N, 2-Conductor, 2-Hole, Heavy Duty Copper Lug

By Burndy
Catalog # [Q2B312N](#)



2-Conductor, 250-350 kcmil, 2-Hole, 1/2" Stud, 1.75" Spacing,
Cables at right angles to terminal block

Features

- QIKLUG™ terminals for copper cable
- High copper alloy
- Q2B style lugs join two cables at right angles to a single terminal block
- Each element accommodates a range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 250 kcmil • 300 kcmil • 350 kcmil
Conductor Size	250-350 kcmil
Number Of Conductors	2
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	250 kcmil-350 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Clamping Elements	2
Connector Type	Right Angle

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width fraction	2-3/8 in
--------------------------------	----------

Dimension - Pad Width inch	2.38 in
Package Height	0.000 in
Dimension - Height mm	42.9 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.69 in
Dimension - Height fraction	1-3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.69 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	9/16
Dimension - Bolt Size fraction	9/16
Dimension - B Length fraction	1-3/16 in
Dimension - Width mm	60 mm
Dimension - Width inch	2.38 in
Dimension - B Length inch	1.19 in
Dimension - D inch	3.19 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	5.88 in

Force Related

Installation Torque Recommended in-lb	325 LBS/in
---------------------------------------	------------

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810324868
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Bright Dipped
UPC 12 Digit	781810324868
UPC 14 Digit GTIN	00781810324868

Logistics

Minimum Pack Quantity	32
Pallet Quantity	1
Carton Quantity	1



A Hubbell brand