



QA1CBNK, 1-Hole, Heavy Duty Copper Terminal, Nickel Plated

By Burndy
Catalog # QA1CBNK



#4-1 AWG Str, 1-Hole, 1/4" Stud, Single Clamping Element, Compact Design, Nickel Plated

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Navy Size Range	30 (19) Navy-75 (37) Navy
Conductor - Copper Str Navy Size	• 30 (19) Navy • 40 (19) Navy • 50 (19) Navy • 60 (37) Navy • 75 (37) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	4 AWG-1 AWG
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type	Single Clamp
----------------	--------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	0.62 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - D inch	0.75 in
Dimension - N inch	0.34 in
Dimension - Hole Size inch	0.28 in
Dimension - Length Overall inch	1.75 in

General

Plated	Y
Trade Name	QIKLUG™
UPC	781810500132
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Nickel Plated
UPC 12 Digit	781810500132
UPC 14 Digit GTIN	00781810500132

Logistics

Minimum Pack Quantity	24
-----------------------	----

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)