



QA262N, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA262N](#)

1/0-2/0 Str, 2-Hole, 1/2" Stud, 1.75" Spacing, Single Clamping
Element, Compact Design



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG
Conductor Size	2/0-1/0 AWG
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	1/0 -2/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.00 in
Package Height	0.000 in
Dimension - Height mm	29.5 mm

Dimension - Height inch	1.16 in
Dimension - Height fraction	1-4/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	106 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - B Length fraction	47/50 in
Dimension - Width inch	0.81 in
Dimension - B Length inch	0.94 in
Dimension - Cross Flats inch	0.69 in
Dimension - D inch	3.12 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	4.19 in

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810314524
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810314524
UPC 14 Digit GTIN	00781810314524

Logistics

Minimum Pack Quantity	7
Pallet Quantity	4500
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)

