

QB312N, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QB312N](#)

250-350 kcmil, 2-Hole, 1/2" Stud, 1.75" Spacing, Right Angled (Side Entry) Connector



Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 250 • 300 • 350
Conductor Size	250-350 kcmil
Number Of Conductors	1
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	250-350

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Clamping Elements	1
Connector Type	Right Angle

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Dimension - Height mm	42.9 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.69 in
Dimension - Height fraction	1-11/16

Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	114 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Dimension - B Length fraction	1-15/79 in
Dimension - Width mm	30 mm
Dimension - Width inch	1.19 in
Dimension - B Length inch	1.19 in
Dimension - D inch	3.25 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	4.50 in

Force Related

Installation Torque Recommended in-lb	325 LBS/in
---------------------------------------	------------

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
UPC	781810324660
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810324660

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)