



QDA40

by Burndy
Catalog ID: QDA40

Prop 65 Notice

Cast Copper Alloy Qiklug, 600 - 800 kcmil Commercial. 650 - 800 Navy, 4-3/16 in L, 2-1/8 in W.

Features: Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Studs, Provides Low Contact Resistance When Gripped Between Two Contact Nuts, One Wrench Installation, Dimension K: 1-1/16 IN, Dimension T: 3/8 IN, Stud/bolt Hole Size: 1 IN, Tongue Width: 2-1/8 IN, Conductor Type: Run: Navy, Commercial Stranded Copper, Installation Torque: 500 IN-LB, Height: 2-5/16 IN, Length: 4-3/16 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Studs
Connector Type	Terminal
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325643

Dimensions

Dimension - Height fraction	2-5/16 in
Dimension - Height inch	2.31 in
Dimension - Hole Size inch	1.13 in
Dimension - Hole Size mm	27 mm
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.19 in
Dimension - Pad Width inch	2.12 in
Dimension - Stud Size inch	1
Dimension - Width inch	2.13
Dimension - Width mm	54 mm

Conductor Related

Conductor - Copper Str Navy Size	650 (127) Navy;800 (127) Navy
----------------------------------	-------------------------------

Conductor - Copper Str Navy Size Range	650 (127) Navy-800 (127) Navy
Conductor - Copper Str Size	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	600 kcmil-800 kcmil
Conductor Type	• CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)