

Substation - Copper Bar Tap

By Burndy
Catalog # [QGFL26B2](#)

Substation Connectors



Features

- High copper alloy BARTAP™ for joining a range of cable to bar or pad
- Can be installed side by side or in-line on NEMA drilled bar
- 1-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• #8 Sol • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • #2/0 Str
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG

Conductor - Copper Solid Size Range	8 AWG-2/0 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	#8 Sol-#2/0 Str

Configuration

Connector Type	Bus Bar Clamp and Accessories
----------------	-------------------------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	58.9 mm
Dimension - Height inch	2.32 in
Dimension - Height fraction	2-8/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	1-1/8 in
Dimension - B Length fraction	1-1/4 in
Dimension - Width mm	29 mm
Dimension - Width inch	1.13 in
Dimension - B Length inch	1.25 in

General

Trade Name	BARTAP™
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Sub Brand	BARTAP
UPC	781810005903
Type	QGFL
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810005903
UPC 14 Digit GTIN	00781810005903

Logistics

Pallet Quantity	3600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)