



QGFL29B1T6, Bartap, Cable to Flat, #6 Str-250 kcmil

By Burndy
Catalog # QGFL29B1T6

Substation Connectors

Features

- High copper alloy BARTAP™ for joining a range of cable to bar or pad
- Can be installed side by side or in-line on NEMA drilled bar
- 1-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct	Yes
Burial	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• #6 Str • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	#6 Str-250 kcmil

Configuration

Connector Type Bus Bar Clamp and Accessories

Dimensions

Package Height	4.5 in
Dimension - Height mm	79.5 mm
Dimension - Height inch	3.13 in
Dimension - Height fraction	3-1/8 in
Package Weight	13 lb.
Package Length	7.06 in
Package Width	6.13 in
Dimension - Width fraction	1-3/8 in
Dimension - B Length fraction	1-5/8 in
Dimension - Width mm	35 mm
Dimension - Width inch	1.38 in
Dimension - B Length inch	1.63 in

General

Trade Name	BARTAP™
Material - Hardware	DURIUM™ Silicon Bronze
Plated	No
Sub Brand	BARTAP
Product Type	Mechanical
UPC	781810005910
Type	QGFL
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810005910
UPC 14 Digit GTIN	00781810005910

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)