



QGFL34B1, Bartap, Cable to Flat, 1/0 Sol-500
kcmil

By Burndy
Catalog # QGFL34B1

Substation Connectors



Features

- High copper alloy BARTAP™ for joining a range of cable to bar or pad
- 1-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Solid Size	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	1/0 -500 kcmil

Configuration

Connector Type	Bus Bar Clamp and Accessories
----------------	-------------------------------

Dimensions

Package Height	4.5 in
Dimension - Height mm	79.5 mm
Dimension - Height inch	3.13 in
Dimension - Height fraction	3-1/8 in
Package Weight	11.04 lb.
Package Length	6.13 in
Package Width	4.56 in
Dimension - Width fraction	1-3/4 in
Dimension - B Length fraction	2 in
Dimension - Width mm	44 mm
Dimension - Width inch	1.75 in
Dimension - B Length inch	2.00 in

General

Trade Name	BARTAP™
Material - Hardware	DURIUM™ Silicon Bronze
Plated	No
Sub Brand	BARTAP
Product Type	Mechanical
UPC	781810325155
Type	QGFL
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810325155
UPC 14 Digit GTIN	00781810325155

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1920
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)