

Substation - Copper Bar Tap

By Burndy
Catalog # [QGFL39B1](#)

Substation Connectors



Features

- High copper alloy BARTAP™ for joining a range of cable to bar or pad
- 1-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct	Yes
Burial	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	350 kcmil-750 kcmil
Conductor - Copper Str Size	• 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil

Configuration

Connector Type

Bus Bar Clamp and Accessories

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.6 mm
Dimension - Height inch	3.25 in
Dimension - Height fraction	3-1/4 in
Dimension - B Length fraction	2-1/4 in
Package Weight	0.000 lb.
Dimension - Width mm	44 mm
Dimension - Width inch	1.75 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.25 in
Dimension - Width fraction	1-3/4 in

General

Plated	N
Trade Name	BARTAP™
Material - Hardware	DURIUM™ Silicon Bronze
Sub Brand	BARTAP
UPC	781810005880
Type	QGFL
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810005880
UPC 14 Digit GTIN	00781810005880

Logistics

Pallet Quantity	1440
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)