



# QN10F25X03B, Nylon Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy  
Catalog # [QN10F25X03B](#)



Nylon Female Quick Disconnect For 12 - 10 AWG (.25 x .03).

### Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

### General

|                   |                         |
|-------------------|-------------------------|
| Catalog Number    | QN10F25X03B             |
| Connector Type    | Female Quick Disconnect |
| Insulation        | Y                       |
| Insulation Type   | Nylon                   |
| Material          | Brass                   |
| Plated            | Y                       |
| Plating Type      | Tin                     |
| Trade Name        | FINGRIP™                |
| UPC               | 781810292921            |
| UPC 14 Digit GTIN | 00781810292921          |

### Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - B Length fraction             | 3/13 in |
| Dimension - B Length inch                 | 0.23 in |
| Dimension - F Width Center to Center inch | 0.13 in |
| Dimension - Length Overall inch           | 0.97 in |

### Conductor Related

|                                   |               |
|-----------------------------------|---------------|
| Conductor - Copper Str Size       | 12 AWG;10 AWG |
| Conductor - Copper Str Size Range | 12 AWG-10 AWG |
| Conductor Size                    | 12 - 10 AWG   |
| Conductor Type                    | CU C Str-Size |

### Certifications And Compliance

|                                |       |
|--------------------------------|-------|
| Certification - ETL            | No    |
| Certification - UL Recognized  | No    |
| Certification - cULus          | Yes   |
| Industry Standard(s)           | UL467 |
| Standards - Industry Standards | UL310 |
| Met                            |       |
| Standards - RoHS Compliance    | CM    |
| Status                         |       |
| UL Listed                      | No    |

### Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 500   |
| Minimum Pack Quantity | 500   |
| Pallet Quantity       | 99999 |

### Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - QN10F25X03B](#)



A Hubbell brand