



QN10M25X03D, Nylon Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # QN10M25X03D

Nylon Male Quick Disconnect For 12 - 10 AWG (.25 x .03)



Features

- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Mates with dimpled female socket detent ensuring firm grip

Application

Male Disconnect

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Current

Voltage - Maximum	300 V
-------------------	-------

Dimensions

Dimension - Width inch	0.25 in
Package Length	0.000 in
Dimension - Width mm	6 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.95 in

General

Sub Brand	HYDENT
Insulation Type	Nylon
Trade Name	FINGRIP™
Plated	Y
Insulation Type	Y
Type	Disconnect Connectors
UPC 12 Digit	781810525043
UPC 14 Digit GTIN	00781810525043
Material	Brass
Plating Type	Tin
UPC	781810525043

Logistics

Minimum Pack Quantity	50
Carton Quantity	600

Product Assets

[Catalog \[English\]](#)