



QN14F11X02D, Nylon Female Quick Disconnect For 16 - 14 AWG (.11 x .02)

By Burndy
Catalog # [QN14F11X02D](#)

Nylon Female Quick Disconnect For 16 - 14 AWG (.11 x .02)



Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

Application

Female Disconnect

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Under Review
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	UI
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type Female Quick Disconnect

Current

Voltage - Maximum 300 V

Dimensions

Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.77 in

General

Sub Brand	FINGRIP
Insulation Type	Nylon
Trade Name	FINGRIP™
Plated	Y
Insulation Type	Y
Type	Disconnect Connectors
UPC 12 Digit	781810525616
UPC 14 Digit GTIN	00781810525616
Material	Brass
Plating Type	Tin
UPC	781810525616

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)