



QN14F18X02D, Nylon Female Quick Disconnect For 16 - 14 AWG (.19 x .02)

By Burndy
Catalog # [QN14F18X02D](#)

Nylon Female Quick Disconnect For 16 - 14 AWG (.19 x .02)



Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

Application

For quickly connecting or disconnecting a terminal

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Current

Voltage - Maximum	300 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm
Dimension - Length Overall inch	0.79 in

General

Insulation Type	Nylon
Trade Name	FINGRIP™
Insulation	Y
Sub Brand	FINGRIP
Plated	Y
Type	Disconnect Connectors
UPC 12 Digit	781810293409
UPC 14 Digit GTIN	00781810293409
Material	Brass
Plating Type	Tin
UPC	781810293409

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)