



# QN14F25X03B, Nylon Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy  
Catalog # [QN14F25X03B](#)



Nylon Female Quick Disconnect For 16 - 14 AWG (.25 x .03).

### Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

### General

|                   |                         |
|-------------------|-------------------------|
| Catalog Number    | QN14F25X03B             |
| Connector Type    | Female Quick Disconnect |
| Insulation        | Y                       |
| Insulation Type   | Nylon                   |
| Material          | Brass                   |
| Plated            | Y                       |
| Plating Type      | Tin                     |
| Trade Name        | FINGRIP™                |
| Type              | Disconnect Connectors   |
| UPC               | 781810292785            |
| UPC 14 Digit GTIN | 00781810292785          |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Length Overall inch | 0.87 in |
| Dimension - Strip Length inch   | 3/8 in  |
| Dimension - Width inch          | 0.25 in |
| Dimension - Width mm            | 6 mm    |

### Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 300 V |
|-------------------|-------|

### Conductor Related

|                 |                    |
|-----------------|--------------------|
| Conductor Range | #16 AWG to #14 AWG |
| Conductor Size  | 16 - 14 AWG        |
| Conductor Type  | CU C Str-Size      |

### Certifications And Compliance

|                                |       |
|--------------------------------|-------|
| Certification - ETL            | No    |
| Certification - UL Recognized  | No    |
| Certification - cULus          | Yes   |
| Industry Standard(s)           | UL467 |
| Standards - Industry Standards | UL310 |
| Met                            |       |
| Standards - RoHS Compliance    | CM    |
| Status                         |       |
| UL Listed                      | No    |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1000 |
|-----------------------|------|

### Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50094210](#)  
[Specifications - QN14F25X03B](#)