



QN14FF187D

By Burndy
Catalog # [QN14FF187D](#)



General

Catalog Number	QN14FF187D
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	FINGRIP
Type	Disconnect Connectors
UPC	781810087954
UPC 12 Digit	7818100879544

Dimensions

Dimension - B Length fraction	2/25 in
Dimension - B Length inch	0.08 in
Dimension - D inch	0.16 in
Dimension - Pad Width inch	0.32 in
Dimension - Thread Size	-
Dimension - Width mm	0 mm

Conductor Related

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.