



QN14FF250D, Nylon Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy
Catalog # [QN14FF250D](#)



Nylon Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

Features

- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Mates with dimpled female socket detent ensuring firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	19/50 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.38 in
Dimension - Pad Width inch	0.23 in
Package Height	0.000 in
Dimension - Length Overall inch	0.89 in
Dimension - D inch	0.16 in

General

Insulation Type	Nylon
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 14 Digit GTIN	00781810038345
Material	Brass
Plating Type	Tin
UPC	781810038345

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)