



Oh No!
IMAGE COMING SOON

QN14MF250CD

By Burndy
Catalog # [QN14MF250CD](#)

Specifications

Certification - ETL	No
Certification - UL Recognized	N
Standards - RoHS Compliance Status	CM
Certification - cULus	N
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size Range	N/A
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG 14 AWG

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	9/20 in
Package Weight	0.000 lb.

Dimension - Width mm	0 mm
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.45 in
Dimension - D inch	0.17 in
Dimension - Thread Size	-
Dimension - Length Overall inch	0.97 in

General

Plated	Y
Insulation Type	Nylon
Trade Name	FINGRIP
UPC	781810020777
Type	Disconnect Connectors
Insulation	Y
Material	Brass
Plating Type	Tin
UPC 12 Digit	781810020777
UPC 14 Digit GTIN	00781810020777

Logistics

Pallet Quantity	72000
Carton Quantity	300

Product Assets

[Catalog \[English\]](#)